



## ChemSplash® 2

Heavy-duty chemical splash coveralls protect against aggressive chemicals, acids, & caustics.


These durable and disposable coveralls are designed with lighter fabric that provides superior protection against a broad range of acids, caustic chemicals, and blood penetration. Our proprietary fabric is lighter and more pliable than competitive coveralls, so users can work comfortably all shift long. Taped seams provide superior protection to coveralls made with serged seams. Possible applications include emergency response, chemical loading, petrochemical environments, & more.

### Available Garments




Coverall with Elastic Wrists, Open Ankles, Storm Flap over Zipper with Pressure-Sensitive Tape, Taped Seams, Attached Thumb Loops, Large Zipper Pull

#7312GT  
Sizes: Medium - 4XL  
6 per case



Coverall with Attached Respirator Hood, Elastic Wrists, Storm Flap over Zipper with Pressure-Sensitive Tape, Taped Seams, Attached Thumb Loops, Large Zipper Pull

#7315GT  
Sizes: Medium - 4XL  
6 per case



Coverall with Attached Respirator Hood & Boots, Elastic Wrists, Storm Flap over Zipper with Pressure-Sensitive Tape, Taped Seams, Attached Thumb Loops, Large Zipper Pull

#7319GT  
Sizes: Medium - 4XL  
6 per case

### Agent Testing

CHEMICAL ASTM F1001	CAS NUMBER	PENETRATION ASTM F903-10
ACETONE	67-64-1	PASS
ACETONITRILE	75-05-8	PASS
CARBON DISULFIDE	75-15-0	PASS
DICHLOROMETHANE	75-09-2	PASS
DIETHYLAMINE	109-89-7	PASS
ETHYL ACETATE	141-78-6	PASS
ISOPROPANOL (99.9%)	67-63-0	PASS
METHANOL	67-56-1	PASS
N,N-DIMETHYLFORMAMIED	68-12-1	PASS
N-HEXANE	110-54-3	PASS
N-HEPTANE	142-82-5	PASS
NITRIC ACID	7697-37-2	PASS
NITROBENZENE	98-95-3	PASS
SODIUM HYDROXIDE (50%)	1310-73-2	PASS
SULFURIC ACID (96.3%)	7664-93-9	PASS
TETRACHLOROETHYLENE	127-18-4	PASS
TETRAHYDROFURAN	109-99-9	PASS
TOLUENE	108-88-3	PASS

### Physical Properties

TEST CONDUCTED	TEST METHOD	RESULTS
Weight, oz/y <sup>2</sup>	ASTM D-3776	2.9 oz/y <sup>2</sup>
Tensile Strength - Machine Direction	ASTM D-5034	51.2 lbs
Tensile Strength - Cross Direction	ASTM D-5034	36.2 lbs
Tear Strength, Trapezoid Machine Direction	ASTM D-5733	23.3 lbs
Tear Strength, Trapezoid Cross Direction	ASTM D-5733	15.4 lbs
Ball Burst Strength	ASTM D-751	52 lbs

### Additional Agent Testing

CHEMSPLASH® 2 ALSO PROTECTS AGAINST THE FOLLOWING AGENTS
Bloodborne Pathogens - ASTM F1671-13
Synthetic Blood - ASTM F1670-14
JP-8 Jet Fuel - ASTM F903-10

### ISO 6530 : 2005 Protective clothing - Protection against liquid chemicals - Test method for resistance of materials to penetration by liquids

TEST LIQUID & CONCENTRATION	VOLUME OF TEST LIQUID (cm <sup>3</sup> )	FLOW RATE cm <sup>3</sup> /s	RESULTS					
			PENETRATION INDEX I <sub>P</sub>		REPELLENCY INDEX I <sub>R</sub>		ABSORPTION INDEX I <sub>A</sub>	
			LENGTH	WIDTH	LENGTH	WIDTH	LENGTH	WIDTH
N-Heptane 99%	10±0.5	1.0	0.0%	0.0%	95.2%	96.2%	4.8%	3.8%
Isopropanol 99.5%	10±0.5	1.0	0.0%	0.0%	95.6%	95.4%	4.4%	4.6%

## Benefits



### Enhanced Safety

A storm flap over the zipper with pressure-sensitive tape, along with taped seams, help prevent liquids and other contaminants from entering the suit via otherwise exposed seams.



### All-day Comfort

Unlike traditional bulky chemical suits, our chemical suits are made of a lighter more pliable fabric making it more breathable and easier to move.



### Move with Ease

An elastic back stretches with the wearer for more comfort and better tear resistance.



### Convenience Features

Attached thumb loops prevent sleeves from riding up while a large zipper pull is easier to grab with gloved hands.

**Electrostatic Properties:  
EN 1149-5-2018 - Part 1: Meets Requirement**