



## GammaGuard® CE

Sterile garments made of a comfortable fabric with a superior liquid and particulate barrier.

All GammaGuard CE® garments are individually packaged and sterilized to a 10<sup>-6</sup> sterility assurance level (SAL). This helps prevent workplace contamination and cross contamination of products or materials. Low-linting fabric helps reduce the release of unwanted particulates, while tunnelized elastic also contains particle shed.

### Available Garments



#### Coverall with Tunnelized Wrists & Ankles

#CE11013CIS  
Sizes: Small - 4XL  
25 per case



#### Frock, No Pockets, Tunnelized Wrists

#CE11026CIS  
Small - 4XL  
50 per case



#### Full Face Hood with Tunnelized Elastic Face

#CE11063CIS  
Size: Universal  
100 per case



#### Sleeves, 21.5" Length Tunnelized Elastic on Both Ends

#CE11065CIS  
Size: Universal  
100 pairs per case



#### Shoe Covers

#CE11101CIS  
Size Large with Non-Skid Soles  
200 pairs per case

#CE11102CIS  
Size XL with Non-Skid Soles



#### Boot Covers

#CE11104CIS  
Size Large with Non-Skid Soles  
100 pairs per case

#CE11106CIS  
Size XL with Non-Skid Soles



#### Coverall with Attached Hood & Boots

#CE11019CIS  
Sizes: Small - 4XL  
25 per case

### Benefits

In a cleanroom environment, maintaining sterility is critical for keeping products, processes, and materials contamination-free. GammaGuard® CE cleanroom apparel is designed with varying levels of protection to help keep you safe based on your cleanroom standards.

All garments and cleanroom suits are clean processed using the Sterile-Don™ packaging process, meaning all loose particles have been removed from the clothing before packaging.

### Physical Testing

TEST	METHOD	RESULT
Weight, oz/y <sup>2</sup>	ASTM D3776	1.8
Ball Burst Strength (lbs)	ASTM D3787	21
Tensile Strength (lbs) Machine Direction	ASTM D5034	15
Tensile Strength (lbs) Cross Direction	ASTM D5034	24.5
Tensile Strength (lbs) Trapezoidal - Machine Direction	ASTM D1117	2.4
Tensile Strength (lbs) Trapezoidal - Cross Direction	ASTM D1117	5.6
Air Permeability (cfm)	ASTM D737	<0.55
Helmke Drum Particle Test	IEST-RP-CC003	Category 1




**Bound Seams**





**Tunnelized Elastic**





**Sterility Assurance**


- 

**Raise your Standards**  
GammaGuard® CE is made in an ISO-13485 certified facility. All garments are sterilized to a 10<sup>-6</sup> SAL.
- 

**Trust the Process**  
Sterile-Don™ packaging protects against contamination during donning.
- 

**Decrease Particle Shed**  
Tunnelized elastic is encapsulated to capture particle shed & eliminate raw edges that can generate particulates.
- 

**Tear-resistant Fabric**  
Our proprietary fabric is tear-resistant and keeps users cooler than competitive fabrics.
- 

**Quality Assurance**  
A certificate of sterility is included in each case.
- 

**Bound Seams are Strong Seams**  
A reinforced outer binding is tightly sewn over each seam to strengthen it & eliminate raw edges that can generate particulates.